
Hideaway HSA 300

HSA - HIDEAWAY SURFACE ACCESS ENCLOSURE WITH AV CONNECTIVITY, AC POWER, AND USB POWER











Central Europe

Multi-Region

The Extron Hideaway® HSA 300 is a compact, tilt-up, furniture mountable enclosure for convenient access to AV connectivity, AC power, and USB power. It offers a perfect blend of connectivity and design aesthetics that complements sophisticated board rooms, conference rooms, and training facilities.

- Provides convenient access to HDMI, VGA, Stereo Audio, and Network connectivity
- Provides two 5 VDC USB power outlets and up to 2.1 A / 10.5 watts of power for charging mobile devices
- Unswitched AC power outlets available for US, Europe, and other world markets
- Available Multi-Region AC outlet is compatible with a variety of AC plug types
- Durable mechanic pneumatic movement and mechanical latching mechanism
- Virtually flush with the furniture surface when closed
- ▶ UL/c-UL listed and CE compliant




DESCRIPTION

The Extron **Hideaway® HSA 300** is a compact, tilt-up, furniture-mountable enclosure for inconspicuous access to AV connectivity, AC power, and USB power. The HSA 300 features connectors for HDMI, VGA, Stereo Audio, and Network signals, one unswitched AC outlet, and two 5 VDC USB power outlets for charging mobile devices such as smartphones or tablets. When closed, the HSA 300 sits virtually flush with the table surface. To open, press the top of the enclosure and the HSA 300 slowly pivots into view, presenting the connectors at an ergonomic 49 degree angle to the tabletop. The HSA 300 is available with one US, UK, Central Europe, or Multi-Region AC outlet that's compatible with a variety of AC plug types. The HSA 300 is available in a durable black anodized finish to complement most furniture styles and room decor.

FEATURES

- Provides convenient access to HDMI, VGA, Stereo Audio, and Network connectivity
- Provides two 5 VDC USB power outlets and up to 2.1 A / 10.5 watts of power for charging mobile devices
- Unswitched AC power outlets available for US, Europe, and other world markets
- Available Multi-Region AC outlet is compatible with a variety of AC plug types
- ▶ Durable mechanic pneumatic movement and mechanical latching mechanism
- ▶ Virtually flush with the furniture surface when closed
- ▶ UL/c-UL listed and CE compliant

APPLICATION DIAGRAM



SPECIFICATIONS

VIDEO INPUT/	OUTPUT		
Number/signal typ	e	1 pass-through VGA	
		1 pass-through HDMI	
Connectors		15-pin HD female to 15-pin HD female on a	6" (15 cm)
		pigtail	
		HDMI female to HDMI female on a 10" (25 c	m) pigtail
AUDIO INPUT/	OUTPUT		
Number/signal typ	е	1 pass-through stereo, unbalanced	
Connectors		3.5 mm TRS jack to 3.5 mm 3 pole captive s	screw
		connector on a 10" (25 cm) pigtail	
DATA INPUT/O	UTPUT		
Standards		CAT 6, TIA/EIA T568B	
Connectors		1 female RJ-45 to 1 female RJ-45	
GENERAL			
Power			
HSA 300 (US)		125 VAC, 50-60 Hz, 12 A max.	
HSA 300 (EU/Multi-F	Region/UK)	240 VAC, 50-60 Hz, 10 A max.	
USB power			
Power supply		External	
		Input: 100-240 VAC, 50-60 Hz	
Danier and A		Output: 12 VDC, 1 A	
Power output		USB: 5 VDC, 2.1 A, 10.5 watts total	
Mounting Furniture mount		Voo	
	-lm-a-a	Yes 0.375" to 3.00" (0.95 cm to 7.62 cm)	
Min./max. table thickness			
Enclosure type	UNITOO	,	
Enclosure type		Metal	
Enclosure dimensi	ons	Metal	t dimancione
Enclosure dimension CAUTION: Use the	ons e appropriate metal Extron	Metal routing template or refer to the surface cutout	
Enclosure dimension CAUTION: Use the here before cutting a	ons e appropriate metal Extron a hole in the furniture or otl	Metal routing template or refer to the surface cutout her surface. Pay special attention to the directi	ion the
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The co	ons e appropriate metal Extron a hole in the furniture or otl	Metal routing template or refer to the surface cutout	ion the
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes.	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the	Metal routing template or refer to the surface cutout her surface. Pay special attention to the directi	ion the
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo	ons e appropriate metal Extron a hole in the furniture or ot onnector access side of the	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction unit is underlined. Extron is not responsible for	ion the or miscut
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim)	ons e appropriate metal Extron a hole in the furniture or other unnector access side of the	Metal routing template or refer to the surface cutout her surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for 8.18" W x 6.375" D (20.79 cm W x 16.19 cm	ion the or miscut em D)
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for 8.18" W x 6.375" D (20.79 cm W x 16.19 cm 5.90" W x 4.10" D (14.99 cm W x 10.41 cm	or miscut or miscut om D)
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim)	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for 8.18" W x 6.375" D (20.79 cm W x 16.19 cm	ion the or miscut om D) on D)
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction unit is <u>underlined</u> . Extron is not responsible for the surface. Extron is not responsible for the surface of	ion the or miscut om D) on D)
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	routing template or refer to the surface cutout her surface. Pay special attention to the direction unit is <u>underlined</u> . Extron is not responsible for the surface. Extron is not responsible for the surface of the su	ion the or miscut im D) n D) D 0.05 +cm D
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for surface. Pay Special attention to the direction it is underlined. Extron is not responsible for surface. Extra is underlined in the surface cutout is underlined. Extra is underlined in the surface cutout is underlined. Extra is underlined in the surface cutout is underlined. Extra is underlined in the surface cutout is underlined. Extra is underlined in the surface cutout is underlined. Extra is unde	ion the or miscut im D) n D) D 0.05 +cm D
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for surface. Pay Special attention to the direction it is underlined. Extron is not responsible for surface. Extron W x 16.19 cm Surface. Extra	ion the or miscut m D) n D) D 0.05 +cm D
Enclosure dimensi CAUTION: Use the here before cutting a unit will face. The comounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for surface. Pay special attention to the direction it is underlined. Extron is not responsible for surface. Extron W x 16.19 cm S.390" W x 4.10" D (14.99 cm W x 10.41 cm 7.70 +0.00/-0.02" W x 5.90 +0.00/-0.02" (19.56 +0.00/-0.05 +cm W x 14.99 0.00/-14.0" H x 6.3" W (front of unit) x 5.0" D (10.2 cm H x 15.9 cm W x 12.7 cm D) without of unit is x 5.0" D	ion the or miscut m D) n D) D 0.05 +cm D
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface)	ons e appropriate metal Extron a hole in the furniture or oth unnector access side of the dels plate)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for 5.90" W x 4.10" D (14.99 cm W x 10.41 cm 7.70 +0.00/-0.02" W x 5.90 +0.00/-0.02" (19.56 +0.00/-0.05 +cm W x 14.99 0.00/-4.0" H x 6.3" W (front of unit) x 5.0" D (10.2 cm H x 15.9 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D) with 10.2 cm H x 25.3 cm W x 12.7 cm D)	ion the or miscut m D) n D) D 0.005 +cm D out clamps clamps
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface)	ons e appropriate metal Extron a hole in the furniture or ot onnector access side of the dels plate) le rim)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for unit is underlined. Extron is not responsible for 5.90" W x 4.10" D (14.99 cm W x 10.41 cm 7.70 +0.00/-0.02" W x 5.90 +0.00/-0.02" (19.56 +0.00/-0.05 +cm W x 14.99 0.00/-0.05 +cm W x 14.99 0.00/-0.05 +cm W x 12.7 cm D) without 4.0" H x 15.9 cm W x 12.7 cm D) without 10.2 cm H x 15.9 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm M x 25.0	ion the or miscut m D) n D) D 0.005 +cm D out clamps clamps
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration	ons e appropriate metal Extron a hole in the furniture or ot onnector access side of the dels plate) le rim)	Metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for unit is underlined. Extron is not responsible for 5.90" W x 4.10" D (14.99 cm W x 10.41 cm 7.70 +0.00/-0.02" W x 5.90 +0.00/-0.02" (19.56 +0.00/-0.05 +cm W x 14.99 0.00/-0.05 +cm W x 14.99 0.00/-0.05 +cm W x 12.7 cm D) without 4.0" H x 15.9 cm W x 12.7 cm D) without 10.2 cm H x 15.9 cm W x 12.7 cm D) without 10.2 cm H x 25.3 cm W x 12.7 cm D) without 10.2 cm M x 25.0	ion the or miscut m D) n D) D 0.005 +cm D out clamps clamps
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complia Safety Warranty	ons e appropriate metal Extron a hole in the furniture or ot onnector access side of the dels plate) le rim)	metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for the surface. Pay special attention to the direction it is underlined. Extron is not responsible for the surface. Extron is not responsible for the surface. Extron is not responsible for the surface. Extronois not responsible for the surface. Extra W x 16.19 cm 8.18" W x 6.375" D (20.79 cm W x 10.41 cm 7.70 +0.00/-0.02" W x 5.90 +0.00/-0.02" (19.56 +0.00/-0.02" W x 5.90 +0.00/-0.02" (19.56 +0.00/-0.05 +cm W x 14.99 0.00/-0.05 +cm W x 14.99 0.00/-0.05 +cm W x 12.7 cm D) without the surface is the surface with the surface in the surface is the surface in the surface in the surface is the surface in the surface in the surface is the surface in the surface in the surface in the surface is the surface in the surfa	ion the or miscut im D) n D) D 0.005 +cm D out clamps clamps
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complia Safety	ons e appropriate metal Extron a hole in the furniture or ot onnector access side of the dels plate) le rim)	metal routing template or refer to the surface cutout her surface. Pay special attention to the direction it is underlined. Extron is not responsible for the surface. Pay special attention to the direction it is underlined. Extron is not responsible for the surface. Pay Surface is unit is underlined. Extron is not responsible for the surface. Extron is not responsible for the surface. Extronomorphism with the surface. Extra in the surface is unit is underlined in the surface. Extra in the surface is unit is underlined in the surface is underlined in the surface. Extra in the surface is underlined in the surface is underlined in the surface. Extra in the surface is underlined in the surface is underlined in the surface is underlined in the surface in the surface is underlined in the surface is underlined in the surface in the surface is underlined in the surface in the surface is underlined in the surfa	ion the or miscut m D) n D) D 0.005 +cm D out clamps clamps
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complia Safety Warranty NOTE: All nominal Model	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the dels plate) le rim) ance levels are at ±10%. Version Description	routing template or refer to the surface cutout ther surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for the surface. Pay special attention to the direction unit is <u>underlined</u> . Extron is not responsible for the surface of the su	ion the or miscut Im D) D 0.05 +cm D out clamps clamps Association)
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complia Safety Warranty NOTE: All nominal	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the dels plate) le rim) ance levels are at ±10%. Version Description US Outlet	routing template or refer to the surface cutout ther surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for the surface. Pay special attention to the direction unit is <u>underlined</u> . Extron is not responsible for the surface of the su	ion the or miscut Im D) D 0.05 +cm D out clamps clamps Association)
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complia Safety Warranty NOTE: All nominal Model	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the dels plate) le rim) ance levels are at ±10%. Version Description	routing template or refer to the surface cutout ther surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for \$\frac{8.18"}{5.90"}\$ W x 4.10" D (\frac{14.99}{14.99}\$ cm W x 10.41 cm \frac{7.70}{7.0+0.00/-0.02"}\$ W x 5.90 +0.00/-0.02" (\frac{19.56}{19.56} +0.00/-0.05 + cm W x 14.99 0.00/-4.0" H x \frac{6.3"}{6.3"}\$ W (front of unit) x 5.0" D (10.2 cm H x \frac{15.9}{25.3}\$ cm W x 12.7 cm D) without 4.0" H x \frac{10.0"}{15.90}\$ W (front of unit) x 5.0" D (10.2 cm H x \frac{25.3}{25.3}\$ cm W x 12.7 cm D) without 5.0 lbs (2.3 kg) ISTA 1A in carton (International Safe Transit A) CE, c-UL, CSA C/US, UL 3 years parts and labor	ion the or miscut Im D) In D) D 0.05 +cm D Out clamps clamps Association)
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complis Safety Warranty NOTE: All nominal Model HSA 300 US HSA 300 UK HSA 300 EU	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the dels plate) le rim) ance levels are at ±10%. Version Description US Outlet UK Outlet EU Outlet	routing template or refer to the surface cutout ther surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for \$\frac{8.18"}{5.90"}\$ W x 4.10" D (\frac{14.99}{14.99}\$ cm W x 10.41 cm \frac{7.70}{7.0+0.00/-0.02"}\$ W x 5.90 +0.00/-0.02" (\frac{19.56}{19.56} +0.00/-0.05 + cm W x 14.99 0.00/-4.0" H x 6.3" W (front of unit) x 5.0" D (10.2 cm H x \frac{15.9}{15.9}\$ cm W x 12.7 cm D) without 4.0" H x \frac{10.0"}{15.9}\$ W (front of unit) x 5.0" D (10.2 cm H x \frac{25.3}{25.3}\$ cm W x 12.7 cm D) without 5.0 lbs (2.3 kg) ISTA 1A in carton (International Safe Transit ACE, c-UL, CSA C/US, UL 3 years parts and labor	ion the or miscut Im D) In D) D 0.05 +cm D Out clamps clamps Association) Part numbe 60-1422-04 60-1422-06 60-1422-06 60-1422-06
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complis Safety Warranty NOTE: All nominal Model HSA 300 US HSA 300 UK	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the dels plate) le rim) ance levels are at ±10%. Version Description US Outlet UK Outlet	routing template or refer to the surface cutout ther surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for \$\frac{8.18"}{5.90"}\$ W x 4.10" D (\frac{14.99}{14.99}\$ cm W x 10.41 cm \frac{7.70}{7.0+0.00/-0.02"}\$ W x 5.90 +0.00/-0.02" (\frac{19.56}{19.56} +0.00/-0.05 + cm W x 14.99 0.00/-4.0" H x 6.3" W (front of unit) x 5.0" D (10.2 cm H x \frac{15.9}{15.9}\$ cm W x 12.7 cm D) without 4.0" H x \frac{10.0"}{15.9}\$ W (front of unit) x 5.0" D (10.2 cm H x \frac{25.3}{25.3}\$ cm W x 12.7 cm D) without 5.0 lbs (2.3 kg) ISTA 1A in carton (International Safe Transit ACE, c-UL, CSA C/US, UL 3 years parts and labor	ion the or miscut im D) n D) D 0.005 +cm D out clamps clamps
Enclosure dimensi CAUTION: Use th here before cutting a unit will face. The co mounting holes. HSA 300 — all mo Top plate (outer rim) Top plate (inside tilt Surface cutout (inside Box (under surface) Product weight Vibration Regulatory complis Safety Warranty NOTE: All nominal Model HSA 300 US HSA 300 UK HSA 300 EU	ons e appropriate metal Extron a hole in the furniture or ot nnector access side of the dels plate) le rim) ance levels are at ±10%. Version Description US Outlet UK Outlet EU Outlet	routing template or refer to the surface cutout ther surface. Pay special attention to the directi unit is <u>underlined</u> . Extron is not responsible for \$\frac{8.18"}{5.90"}\$ W x 4.10" D (\frac{14.99}{14.99}\$ cm W x 10.41 cm \frac{7.70}{7.0+0.00/-0.02"}\$ W x 5.90 +0.00/-0.02" (\frac{19.56}{19.56} +0.00/-0.05 + cm W x 14.99 0.00/-4.0" H x 6.3" W (front of unit) x 5.0" D (10.2 cm H x \frac{15.9}{15.9}\$ cm W x 12.7 cm D) without 4.0" H x \frac{10.0"}{15.9}\$ W (front of unit) x 5.0" D (10.2 cm H x \frac{25.3}{25.3}\$ cm W x 12.7 cm D) without 5.0 lbs (2.3 kg) ISTA 1A in carton (International Safe Transit ACE, c-UL, CSA C/US, UL 3 years parts and labor	ion the or miscut Im D) In D) D 0.05 +cm D Out clamps clamps Association) Part numbe 60-1422-04 60-1422-06 60-1422-06 60-1422-06

For complete specifications, please go to www.extron.com Specifications are subject to change without notice.

- Worldwide Sales Offices

Anaheim • Raleigh • Silicon Valley • Dallas • New York • Washington, DC • Toronto • Mexico City • Paris • London • Frankfurt Amersfoort • Moscow • Dubai • Johannesburg • New Delhi • Bangalore • Singapore • Seoul • Shanghai • Beijing • Tokyo

UNITED STATES	EUROPE	ASIA	MIDDLE EAST
+800.633.9876 Inside USA/Canada	+800.3987.6673 Inside Europe	+800.7339.8766 Inside Asia	+971.4.299.1800
+1 714 491 1500	+31 33 453 4040	+65 6383 4400	